



Wattstopper
LARGE NETWORK ENCLOSURE w/8-PORT SWITCH
Part No. LMNC-0-8



The LMNC is a surface-mount NEMA1-rated enclosure with DIN rails for mounting DLM network components. Comes with hinged cover and provided empty (LMNC-MT) or with 1-9 installed routers. Based on the catalog number suffix, a specific number of NB-ROUTERS and an NB-SWITCH can be installed in the panel and pre-wired to a power supply. Two single outlets are provided on the power supply, one for connecting an LMJA Network Controller plug-in power supply, and a convenience outlet for a laptop or other technician required components.

Features & Benefits

NEMA1-rated enclosure	DIN rail mounting for easy installation or removal of the LMJA Network Controller (ordered separately)
Includes selection of pre-wired NB-ROUTERS and NB-SWITCH	Single termination point for one 120VAC circuit to power all devices
Power supply with two 120V outlets for Network Controller power and laptop or other set up tools	

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Gloss, Painted	UPC Number	754182943791
Country Of Origin	United States	Material	Steel
Product Series	LMNC	Included	8 Network Ports, Data Cables, DIN Rails, Hinged Door, Power Supply, Power Wiring
Number of Knockouts	1	Application Sector	Commercial
Standard	UL, ANSI 61, BAA	Warranty Type	5-Year
Type	Enclosure		

Dimensions

Product Width US	16.0 in	Product Depth US	8.5 in
Product Height US	20.0 in	Enclosure Size	20 in
Knockout Size	1 in		
Trade Programs			
BAA	Yes		
Additional Information			
RoHS Compliant	Yes	Security	Yes
Technical Information			
Compatibility	DLM Wired	Power Supply	120 - 24VAC
Gauge	14	Mounting Hole Type	Keyhole
Enclosure Type	NEMA 1, Network	Configuration	With Switch
Input Voltage	120 VAC	Line Frequency	50 Hz, 60 Hz
Cable Entry	Knockout	Mounting Type	Screw Mount
Location Rating	Dry	Mounting	Wall