



Wattstopper
NEMA1-Rated Small Enclosure for DLM Network Controller/Raccess
Part No. LMNC-ENC1



The LMNC-ENC1 is a surface-mount NEMA1-rated enclosure with a DIN rail for mounting one LMJA Network Controller with a removable cover. The conduit entrances and enclosure sections for high voltage (Class 1) and low voltage (Class 2) wiring are completely separated.

Features & Benefits

NEMA1-rated enclosure	Compatible with LMJA Network Controller, LMBR-650, Network switches and Router.
Shown with LMJA-8xxx-SM installed	Isolated Class 1 and Class 2 wiring
DIN rail mounting for easy installation or removal of Network Controller	

Specifications

General Info

Product Line	Wattstopper	Color	Black, Gray
Finish	Galvannealed	UPC Number	754182944903
Country Of Origin	China	Material	Steel
Product Series	LMNC	Features	Isolated Class 1 and Class 2 Wiring
Included	2 Duplex Grounded Receptacles, Cover, DIN Rails	Number of Knockouts	8
Application Sector	Commercial	Standard	UL, BAA
Warranty Type	5-Year	Type	Enclosure

Dimensions

Product Width US	16.0 in	Product Weight US	12.2 lb
Product Volume US	902.2 cu in	Product Depth US	5.375 in
Product Height US	10.5 in	Enclosure Size	10.5 in
Knockout Size	1/2 in, 3/4 in		

Trade Programs

BAA	Yes
-----	-----

Additional Information

RoHS Compliant	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes		

Technical Information

Compatibility	DLM Wired	Gauge	16
Mounting Hole Type	Punched	Enclosure Type	NEMA 1, Network
Configuration	With Receptacles	Input Voltage	120 VAC
Line Frequency	50 Hz, 60 Hz	Cable Entry	Knockout
Mounting Type	Screw Mount, Surface	Location Rating	Damp
Mounting	Wall		