



Wattstopper
RJ45 Cables, 3 feet, non plenum rated Green
Part No. LMRJ-03



LMRJ Series cables connect Digital Lighting Management (DLM) components without the need for tools or point-to-point discrete wiring. Cables are pre-terminated with industry standard RJ45 connectors compatible with any RJ45 port on DLM components. LMRJ cables utilize B to B wiring.

Features & Benefits

Pre-terminated LMRJ cables for DLM local networks in lengths up to 100 feet

UL and cUL listed and labeled

Wattstopper LM-MSTP wire required for wired segment networks.

This wire is not needed for wireless DLM networks using the wireless bridge (LMBC-600)

Standard green color and markings for DLM provide easy identification of LMRJ cables in plenum

Cables and wire available in a choice of colors for use in exposed locations

LMRJ cables available in plenum and non-plenum rating

Specifications

General Info

Product Line	Wattstopper	Color	Green
UPC Number	754182925087	Country Of Origin	Vietnam
Product Series	LMRJ	Jacket Color	Green with White Stripe
Application Sector	Commercial	Standard	UL, cUL, PEP
Warranty Type	5-Year	Type	Cable

Dimensions

Product Width US	0.6 in	Product Weight US	0.6 lb
------------------	--------	-------------------	--------

Product Volume US	10.8 cu in	Product Height US	0.5 in
Product Length US	36.0 in	Cable Length	3 ft
Additional Information			
RoHS Compliant	Yes	Security	Yes
Technical Information			
Category Performance Application	Cat5e	Wire Gauge	24 AWG
Jacket Application	Standard Non-Rated	Shielded/Unshielded Cable	Unshielded
Termination Style	Pre-Terminated	Conductor	4-Pair Twisted
Cable Type	Booted, Snagless	Jacket Rating	FT4 Rated
Temperature Rating	75° C	Cable Diameter	0.2 in
Indoor/Outdoor	Indoor	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male	Insulation Material	FEP (Fluorinated Ethylene Propylene)