



## Wattstopper Discontinued - Digital Switch, 3-button w/infrared, Black Part No. LMSW-103-B



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

### Features & Benefits

Low voltage pushbutton switches for control of multiple loads

Components of Digital Lighting Management integrated control system

Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors

Customizable buttons with LED status indicators

IR transceiver for wireless configuration and remote control

Plug n' Go automatic configuration and Push n' Learn for personalization

### Specifications

#### General Info

|                    |                            |                    |              |
|--------------------|----------------------------|--------------------|--------------|
| Product Line       | Wattstopper                | Color              | Black        |
| Finish             | Gloss                      | UPC Number         | 754182925544 |
| Country Of Origin  | China                      | Material           | ABS          |
| Product Series     | LMSW                       | Switch Type        | Push         |
| Number of Switches | 3                          | Application Sector | Commercial   |
| Standard           | UL, cUL, FCC part 15, RoHS | Warranty Type      | 5-Year       |
| Type               | Switch                     |                    |              |

#### Dimensions

|                   |            |                   |        |
|-------------------|------------|-------------------|--------|
| Product Width US  | 1.8 in     | Product Weight US | 0.2 lb |
| Product Volume US | 20.3 cu in | Product Depth US  | 1.6 in |
| Product Height US | 4.1 in     |                   |        |

Additional Information

|                |     |          |     |
|----------------|-----|----------|-----|
| RoHS Compliant | Yes | Security | Yes |
|----------------|-----|----------|-----|

Technical Information

|                           |                           |                           |                    |
|---------------------------|---------------------------|---------------------------|--------------------|
| Operating Temperature Min | 0 °C                      | Compatibility             | DLM Wired          |
| Has Battery               | No                        | Operating Temperature Max | 55 °C              |
| Number of Buttons         | 3                         | Number of Rockers         | 0                  |
| Topology                  | Free Topology             | Input Voltage             | 24 VDC             |
| Indoor/Outdoor            | Indoor                    | Mounting Type             | J-Box              |
| Current Draw              | 5 mA                      | Operating Temperature     | 0°-55°C, 32°-131°F |
| Operating Humidity        | 5-95% RH (Non-Condensing) | Location Rating           | Dry                |
| Wire Connection Type      | RJ-45                     | Engraving Type            | Blank              |
| Storage Temperature       | 23° - 176° F, -5° - 80° C |                           |                    |