



**Wattstopper**  
**Discontinued - Digital Switch, 4-button w/infrared, Black**  
Part No. LMSW-104-B



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

## Features & Benefits

|                                                                                             |                                                                          |
|---------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| Low voltage pushbutton switches for control of multiple loads                               | Components of Digital Lighting Management integrated control system      |
| Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors | Customizable buttons with LED status indicators                          |
| IR transceiver for wireless configuration and remote control                                | Plug n' Go automatic configuration and Push n' Learn for personalization |

## Specifications

### General Info

|                    |                            |                    |              |
|--------------------|----------------------------|--------------------|--------------|
| Product Line       | Wattstopper                | Color              | Black        |
| Finish             | Gloss                      | UPC Number         | 754182925599 |
| Country Of Origin  | China                      | Material           | ABS          |
| Product Series     | LMSW                       | Switch Type        | Push         |
| Number of Switches | 4                          | Application Sector | Commercial   |
| Standard           | UL, cUL, FCC part 15, RoHS | Warranty Type      | 5-Year       |
| Type               | Switch                     |                    |              |

### Dimensions

|                           |                           |                           |                    |
|---------------------------|---------------------------|---------------------------|--------------------|
| Product Width US          | 1.8 in                    | Product Weight US         | 0.2 lb             |
| Product Volume US         | 20.3 cu in                | Product Depth US          | 1.6 in             |
| Product Height US         | 4.1 in                    |                           |                    |
| Additional Information    |                           |                           |                    |
| RoHS Compliant            | Yes                       | Security                  | Yes                |
| Technical Information     |                           |                           |                    |
| Operating Temperature Min | 0 °C                      | Compatibility             | DLM Wired          |
| Has Battery               | No                        | Operating Temperature Max | 55 °C              |
| Number of Buttons         | 4                         | Number of Rockers         | 0                  |
| Topology                  | Free Topology             | Input Voltage             | 24 VDC             |
| Indoor/Outdoor            | Indoor                    | Mounting Type             | J-Box              |
| Current Draw              | 5 mA                      | Operating Temperature     | 0°-55°C, 32°-131°F |
| Operating Humidity        | 5-95% RH (Non-Condensing) | Location Rating           | Dry                |
| Wire Connection Type      | RJ-45                     | Engraving Type            | Blank              |
| Storage Temperature       | 23° - 176° F, -5° - 80° C |                           |                    |