



Wattstopper
LightSaver Enclosure 12in X 12in X 4in
Part No. LS-E12



LightSaver Enclosures are suitable for use in housing LightSaver control system components, including control modules (LCO or LCD), and the BT Power Pack. Rated NEMA 1, they are suitable for dry indoor locations, such as electrical rooms or closets.

Features & Benefits

Two sizes of enclosures available

NEMA 1 rated for dry indoor locations

Screw cover

Surface mount

Supplied with pre-mounted DIN rail

Specifications

General Info

Product Line	Wattstopper	Color	Silver
UPC Number	754182921911	Country Of Origin	United States
Material	Steel	Product Series	LS
Included	Cover, DIN Rails	Number of Knockouts	16
Application Sector	Commercial	Warranty Type	5-Year
Type	Enclosure		

Dimensions

Product Width US	2.8 in	Product Weight US	0.3 lb
Product Volume US	28.12 cu in	Product Depth US	1.7 in

Product Height US	2.2 in	Enclosure Size	12 in
-------------------	--------	----------------	-------

Knockout Size	1/2 in, 3/4 in
---------------	----------------

Additional Information

RoHS Compliant	Yes	DesignLights Consortium Qualified System	Yes
----------------	-----	--	-----

Security	Yes
----------	-----

Technical Information

Compatibility	ELCU-100	Mounting Hole Type	Punched
---------------	----------	--------------------	---------

Enclosure Type	Electrical, NEMA 1	Cable Entry	Knockout
----------------	--------------------	-------------	----------

Mounting Type	Screw Mount, Surface	Location Rating	Dry
---------------	----------------------	-----------------	-----

Mounting	Wall
----------	------