



Wattstopper
MSTP Router for LI Controls BASRT-B-WS DIN mounting
Part No. NB-ROUTER



The NB-ROUTER provides a connection point between a single Digital Lighting Management (DLM) segment network and an Ethernet LAN. The router has a rugged metal enclosure with an integral DIN rail mounting clip.

Features & Benefits

Routes one BACnet MS/TP Segment Network to BACnet IP

Simple configuration using a standard web browser

Compatible with DLM Network Controller or third party BACnet building automation systems

BACnet/IP or BACnet Ethernet connectivity

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Painted	UPC Number	754182106189
Country Of Origin	United States	Material	Steel
Product Series	NB	Installation Location	Enclosure, Wall
Application Sector	Commercial	Standard	IP30, RoHS, UL 508, BAA
Warranty Type	1-Year	Type	Network Router

Dimensions

Product Width US	2.74 in	Product Weight US	1.0 lb
Product Height US	1.0 in	Product Length US	4.85 in

Trade Programs

BAA	Yes
-----	-----

Additional Information

RoHS Compliant Yes DesignLights Consortium Qualified System Yes

Security Yes

Technical Information

Operating Temperature Min 32 °F Compatibility DLM Wired

Number of Connections 1 Power Supply 24 VDC/VAC

Operating Temperature Max 140 °F Indicator Network
Status LED,
Power LED

Connector Type RJ-45, RS-485 Input Voltage 24 VDC/VAC

Indoor/Outdoor Indoor Mounting Type DIN Rail

Operating Temperature 0°-60°C, 32°-140°F Operating Humidity 10-95% RH
(Non-
Condensing)

Storage Temperature -40° - 85° C