



Wattstopper
Astronomic Time Switch 24/7 800W, Lt. Almond, Box
Part No. RT-200-LA



The RT-200 Astronomical time clock and timer switch automatically turns lighting or other loads on and off according to user programming. It replaces standard single-pole wall switches for energy savings and security.

Features & Benefits

Turns lights on and off relative to dusk or dawn, or at selected times of day on selected days of the week

Bright OLED display for clear viewing from a wide angle

Shipped in default 2 hour countdown time, easily changed to other lengths or none.

Ideal for any application where precise time-based control is desired

Includes eight programmable control schedules

Ideal for meeting California Title 24 Residential Exterior Astronomical Time-Switch with max 6 hour countdown requirement

Specifications

General Info

Product Line	Wattstopper	Color	Light Almond
UPC Number	754182918508	Country Of Origin	China
Material	Plastic	Features	Single Display, Timer
Switch Type	Push	Installation Location	Wall Box
Application Sector	Commercial	Wall Plate Included	No
Standard	UL, cUL	Warranty Type	5-Year
Type	Timer Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.2491 lb
------------------	--------	-------------------	-----------

Product Volume US	30.015 cu in	Product Depth US	1.8 in
Product Height US	4.1 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Timer Type	Astronomical	Load Rating	1200 W @ 277 VAC, 800 W @ 120 VAC
Horsepower Rating	1/6 HP @ 120 VAC	Frequency Rating	50/60 Hz
Number of Buttons	1	Amperage	4.3 A
Timer Duration	1-6 Hours, 5-30 Minutes	Number of Poles	Single Pole
Requires Neutral Wire	Yes	Timing Range	24-Hour Programmable
On Function	Selectable Auto/Manual	Operating Temperature	32°-122°F
Wire Connection Type	Flying Leads	Voltage	120 VAC, 277 VAC
Connection Type	Wired		