



Wattstopper
Digital Time Switch, 120/277VAC, 0-800W/1200W Ballast, White
Part No. TS-400-W



The IntelliSwitch TS-400 series digital time switches automatically turn lights off after a preset time. The simple pushbutton operation provides users with convenient time out lighting control without the nuisance of twist timers.

Features & Benefits

Automatically turns lights off after preset time	Bright electroluminescent LCD shows timer's countdown
Optional audible or visual alerts before lights turn off	Terminal style wiring for simplified installation
Digital operation and simple pushbutton set-up	Time scroll features allows timer to adjust up or down

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182913725	Country Of Origin	China
Material	Plastic	Features	Single Display, Timer
Switch Type	Push	Installation Location	Wall Box
Application Sector	Commercial	Wall Plate Included	No
Standard	UL, cUL	Warranty Type	5-Year
Type	Timer Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.25 lb
Product Volume US	20.3 cu in	Product Depth US	1.8 in

Product Height US	4.2 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Timer Type	Digital	Load Rating	1200 W @ 277 VAC, 800 W @ 120 VAC
Frequency Rating	50/60 Hz	Number of Buttons	1
Amperage	4.3 A	Timer Duration	1-12 Hours, 5-60 Minutes
Number of Poles	Single Pole	Requires Neutral Wire	No
On Function	Manual On	Operating Temperature	32°-104°F
Wire Connection Type	Flying Leads	Voltage	120 VAC, 277 VAC
Connection Type	Wired		