



Wattstopper
Discontinued - Dual Ctrl 15A Receptacle, Gry
Part No. WRC-15-2-G



Wireless Receptacle Control products facilitate Auto-On/AutoOff occupancy-based control of plug loads without the need to wire receptacles to power packs. A WRC transmitter works with WRC RF-enabled relay-controlled receptacles.

Features & Benefits

Collection consolidated to white option

Duplex receptacles with a choice of one or two controlled outlets

LED indicator communicates status during binding

15A Duplex receptacle, Fully controlled

Labeling meets NEMA requirements for controlled receptacles

The product meets the materials restrictions of RoHS

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	WRC-15-2-W
Color	Gray	UPC Number	754182938827
Country Of Origin	China	Number of Receptacles	2
Features	Dual-Controlled, Indicator Lights	Outlet Type	Controlled
Application Sector	Commercial	Wall Plate Included	No
Standard	UL, cUL	Warranty Type	5-Year

Dimensions

Product Width US	1.7 in	Product Weight US	3.6 oz
Product Volume US	11.0 cu in	Product Depth US	1.54 in
Product Height US	4.2 in		

Additional Information

RoHS Compliant	Yes	Security	Yes
----------------	-----	----------	-----

Technical Information

Compatibility	WRC-TX	Wire Gauge	12 AWG
Is Tamper-Resistant	Yes	Connection Location	Back Only
Number of USBs	0	Frequency Band	915 MHz
Number of Gangs	1	Amperage	15 A
Wireless Range	RF, up to 150 ft (line-of-sight), RF, up to 30 ft (obstructed)	Number of Poles	2 Pole
Is Weather Resistant	No	Indoor/Outdoor	Indoor
Mounting Type	In-Wall	Wire Connection Type	Screw Terminal
Voltage	125 VAC		