



Wiremold
5400 Radiused Full Capacity External Elbow Fitting
Part No. 5418FO



For right angle turns around external corners. Integral dividers provide 2" (51mm) cable bend radius for UTP and Fiber Optic installations. Use this elbow as a radiused alternative to 5418.

Features & Benefits

For right angle turns around external corners. Integral dividers provide 2" (51mm) cable bend radius for UTP and Fiber Optic installations. Use this elbow as a radiused alternative to 5418.

Specifications

General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776540963	Country Of Origin	United States
Material	Plastic	Product Series	5400 Series
Installation Location	On Wall	Application Sector	Commercial
Standard	cULus Listed Raceway: File E90378 Guide RJTX. Complies with flammability requirements of UL-5A. Fittings: File E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to 600V. Meets Section 12-1600 of CEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Fitting		

Dimensions

Product Width US	5.5 in	Product Weight US	1.5 lb
Product Height US	6.9 in	Product Length US	6.9 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E90377	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Is Pre-Wired	No	Indoor/Outdoor	Indoor
--------------	----	----------------	--------

Voltage	600.0 V
---------	---------