



Wiremold
Basic Surge Protector
Part No. 77000N



8 outlet plug-in workstation surge protector

Features & Benefits

8 outlets spaced for plugin transformers

Lighted switch

Impact-resistant putty white polymeric housing

15A

6' (1.8m) 14/3 SJT putty white cord with NEMA 5-15 plug

Maximum surge

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	024006000017	Country Of Origin	China
Product Series	Perma Power	Number of Receptacles	8
Features	Lighted Switch	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	14.0 in	Product Weight US	2.3 lb
Product Height US	1.5 in	Product Length US	4.25 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E111219	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single Stage	Cord Length	6 ft
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	6500 Amps
Response Time	<1 ns	Indoor/Outdoor	Indoor
Wiring Method	Cord-ended	NEMA Configuration Code	5-15P, 5-15R
Mounting Type	Keyhole	Location Rating	Dry
Mounting	Yes	Type of Indicators	LED
Voltage	120.0 V	Environmental Conditions	Indoor, dry location