



Wiremold
861QTC Series Wood Floor Box Assembly
Part No. 861QTCBK



Complete with prewired 15A quad receptacle can be wired as standard or isolated ground. Flush poke-thru-style flanges available in a variety of colors/finishes. Slide covers match painted flange colors. Aluminum and brass covers shipped with black slide covers. Brass flange also available with nonmetallic brass-color slide holder. Die-cast aluminum construction with three 1/2" trade size knockouts: two on the sides and one on the bottom. 18 cu. in. (295 cu.cm) capacity. Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

Features & Benefits

Complete with prewired 15A quad receptacle can be wired as standard or isolated ground.

Flush poke-thru-style flanges available in a variety of colors/finishes

Slide covers match painted flange colors

Aluminum and brass covers shipped with black slide covers

Brass flange also available with nonmetallic brass-color slide holder

Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

Specifications

General Info

Product Line	Wiremold	Finish	Painted
UPC Number	786564013266	Country Of Origin	Mexico
Material	Die-Cast Aluminum	Construction	Assembled
Cover Style	Flush	Number of Knockouts	3
Cover Material	Die-Cast Aluminum	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Weight US	2.5 lb	Product Depth US	4.0 in
Product Height US	3.78 in	Cubic Capacity	18 in³
Knockout Size	1/2 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes		
-------	-----	--	--

Additional Information

RoHS Compliant	Yes		
----------------	-----	--	--

Technical Information

Floor Type	Raised, Wood	Service Capacity	Single
Minimum Floor Depth	1 in	Amperage	15 A
Box Capacity	1 Gang	Cable Entry	Knockout
Number of Outlets	4		