



Wiremold
863DRGFICOM Series Dual Service Floor Box Kit
Part No. 863DRGFICOM



Includes round PVC floor box, one 15A, 125V tamper-resistant decorator style duplex receptacle, one coax F connector, one RJ45 Category 5e connector, and brass duplex opening cover plate with single flip lid.

Features & Benefits

Includes round PVC floor box, one 15A, 125V tamper-resistant decorator style duplex receptacle, one coax F connector, one RJ45 Category 5e connector, and brass duplex opening cover plate with single flip lid.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564054788
Country Of Origin	China	Material	PVC
Construction	Not Assembled	Cover Style	Surface
Cover Material	Brass	Application Sector	Commercial, Residential
Standard	cULus Listed Nonmetallic Outlet Boxes: File E110748 Guide QCMZ. Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Width US	5.75 in	Product Weight US	2.11 lb
Product Depth US	3.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E110748	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Wood	Service Capacity	Dual
------------	------	------------------	------

Box Capacity	2 Gangs	Cable Entry	Through Floor
--------------	---------	-------------	---------------

Number of Outlets	2	Depth Behind Device Plates	3.5 in
-------------------	---	----------------------------	--------