



Wiremold
Omnibox® Series Three Gang Steel Floor Box
Part No. 880S3



The 880S3 three gang Omnibox® Floor Box provides an excellent activation solution for applications where multiple services are required in open space areas. The 880S3 floor box is offered in a stamped steel construction, designed to be installed in above grade concrete floor applications and to meet a wide range of market requirements. This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.

Features & Benefits

TopGuard protection. All cover assemblies for the Omnibox Floor Box Series have TopGuard protection. An integral design which keeps out water, dirt, and debris from the power and communication compartments.

Concrete-tight stamped steel construction. Lower cost option for above grade applications.

Boxes and covers have been listed by Underwriters Laboratories Inc. to their standard UL514A, 514C, 514D, and Canadian standard C22.2

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point-of-use.

Fully adjustable box. Before and after concrete pour adjustability. Lower installed cost.

Three-gang configurations, maximum flexibility. Can remove divider for greater capacity. Supports multiservice applications.

Flush activation assemblies for carpet and tile. Aesthetically pleasing assemblies are interchangeable for both cast-iron and stamped steel.

A wide selection of data and bezel options available for use with Ortronics TracJack and Series II devices.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786564221777	Country Of Origin	Mexico
Material	Steel	Construction	Assembled
Cover Style	Flush	Number of Knockouts	2

Application Sector	Commercial, Education	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box
Dimensions			
Product Width US	7.0 in	Product Weight US	5.278 lb
Product Volume US	336.88 cu in	Product Depth US	13.75 in
Product Height US	3.5 in	Cubic Capacity	180 in ³
Knockout Size	1 in, 1/2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Floor Type	Concrete	Service Capacity	Triple
Box Capacity	3 Gangs	Cable Entry	Knockout
Box Type	Above-Grade	Number of Outlets	0
Depth Behind Device Plates	2.75 in		