



Wiremold
AC Series™ AC8105 Six Gang Raised Floor Box with Gray Carpet Style Lid
Part No. AC8105



The AC Series™ AC8105 Raised Floor Box has a 5 inch (127mm) depth design with an extra 2 inch (51mm) of width for additional wiring capacity and can accommodate four duplex power receptacles on one side. Power plate with duplex knockouts included with box. The communication plate will accept at least three communication adapters for up to 18 ports of activation. Lids rotate 180° for easy orientation. Gray lids are diecast zinc construction and allow for a carpet or tile insert. NOTE: For custom options, consult factory. All boxes are sold with one power plate: 4 inch (102mm) deep boxes have plate with two power duplex receptacle KOs, 5 inch (127mm) deep boxes have plate with four power duplex receptacle KOs. All communication plates sold separately.

Features & Benefits

This product meets the material restrictions of RoHS

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564521181	Country Of Origin	United States
Material	Steel	Construction	Assembled
Number of Knockouts	2	Cover Material	Die-Cast Zinc
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

Dimensions

Product Width US	9.25 in	Product Weight US	12.0 lb
Product Volume US	533.32 cu in	Product Depth US	11.25 in

Product Height US	5.13 in	Cubic Capacity	111 in ³
Knockout Size	1/2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Raised	Service Capacity	Triple
Minimum Floor Depth	5 in	Box Capacity	6 Gangs
Cable Entry	Knockout	Box Type	Recessed
Number of Outlets	0	Depth Behind Device Plates	2 in