



Wiremold
20GB306TRUSB 3' Plugmold® Multioutlet System with USB
Part No. AL20GB306TRUSB



3' Plugmold Multioutlet USB system

Features & Benefits

USB charging. 2.4A USB type A receptacle charges faster than other USB receptacles and is compatible with USB 2.0 and 3.0 type devices.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

This product meets the material restrictions of RoHS.

Tamper-resistant receptacles. Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code® Tamper-Resistant requirements.

Compact design. Eliminates the need for bulky AC adapters.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786776182514	Country Of Origin	United States
Material	Aluminum	Product Series	AL2000 Series
Number of Receptacles	5	Features	USB-A Charging
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail

Standard	cULus Listed Multioutlet assemblies: File E15191 Guide PVGT. Meets Article 380 of NEC.		Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Plugmold		Installed Devices	Single Receptacle, USB-A Ports
Dimensions				
Product Width US	1.125 in		Product Weight US	2.0 lb
Product Depth US	1.12 in		Product Height US	1.4375 in
Product Length US	36.0 in		Receptacle Spacing	6 in
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	E15191		cULus Listed	Yes
Additional Information				
RoHS Compliant	Yes		Product Environmental Profile	Yes
Technical Information				
Is Pre-Wired	Yes		USB Wattage	15 W
USB Amperage	2.4 A		Wiring Configuration	Single Circuit
Number of USBs	1		Amperage	15 A
Indoor/Outdoor	Indoor		Wiring Method	Hard-Wired
NEMA Configuration Code	5-15R		Mounting Type	On Surface
Voltage	125.0 V		Environmental Conditions	Dry interior locations