



Wiremold  
AMTC-4 Series Vertical Drop Aluminum Pole  
Part No. AMTC-4



Two-compartment pole. Nominal material thickness .050" (1.8mm). Length: 10' 5" (3.2m). Furnished unwired without outlets. Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished. NOTE: Custom options - features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.

## Features & Benefits

Two-compartment pole. Nominal material thickness .050" (1.8mm). Length: 10' 5" (3.2m). Furnished unwired without outlets.

NOTE: Custom options - features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.

Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished.

## Specifications

### General Info

|                    |                                                      |                   |                                                            |
|--------------------|------------------------------------------------------|-------------------|------------------------------------------------------------|
| Product Line       | Wiremold                                             | Color             | Silver                                                     |
| UPC Number         | 786776088731                                         | Country Of Origin | United States                                              |
| Material           | Aluminum                                             | Product Series    | Aluminum Tele-Power                                        |
| Application Sector | Commercial                                           | Standard          | cULus Listed, Multioutlet Assemblies: File E15191, E178348 |
| Warranty Type      | 1-Year from Installation or 2-Years from Day of Sale | Type              | Pole                                                       |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 2.25 in | Product Weight US | 13.5 lb |
|------------------|---------|-------------------|---------|

|                   |          |
|-------------------|----------|
| Product Length US | 125.0 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E15191 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Trade Programs

|       |     |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

|                |     |                               |     |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

|        |                         |                    |   |
|--------|-------------------------|--------------------|---|
| Cutout | 2A, A/V, Data, Keystone | Number of Channels | 2 |
|--------|-------------------------|--------------------|---|