



Wiremold
AMTC-415 - AMTC-4 Series Vertical Drop Aluminum Pole
Part No. AMTC-415



Two-compartment pole. Nominal material thickness .050" (1.8mm). Length: 15' 5" (4.7m). Furnished unwired without outlets. Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished. NOTE: Custom options - features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.

Features & Benefits

Two-compartment pole. Nominal material thickness .050" (1.8mm). Length: 10' 5" (3.2m). Furnished unwired without outlets.

Two 8" (203mm) removable covers with KOs for modular jacks and modular furniture communication outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished.

NOTE: Custom options - features such as colors or other lengths (20' (6.1m) maximum) available on custom orders.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786776046496	Country Of Origin	United States
Material	Aluminum	Product Series	Aluminum Tele-Power
Application Sector	Commercial	Standard	cULus Listed, Multioutlet Assemblies: File E15191, E178348
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Pole

Dimensions

Product Width US	2.312 in	Product Weight US	19.4 lb
------------------	----------	-------------------	---------

Product Length US	185.0 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Cutout	2A, A/V, Data, Keystone	Number of Channels	2
--------	-------------------------	--------------------	---