



Wiremold
Wiremold 20GB506TR Tamper Resistant Plugmold Multioutlet System, Black
Part No. BK20GB506TR



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.

Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.

Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.

Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.

Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.

This product meets the material restrictions of RoHS.

Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.

15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.

Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.

Multiple power feed options. Provide clean, attractive installations with concealed power sources.

cULus Listed.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776174854	Country Of Origin	United States
Material	Steel	Product Series	2000 Series
Number of Receptacles	10	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVG7/PVG7

Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Plugmold
Installed Devices	Single Receptacle		
Dimensions			
Product Width US	1.3 in	Product Weight US	3.17 lb
Product Volume US	62.1 cu in	Product Depth US	0.75 in
Product Height US	0.75 in	Product Length US	60.0 in
Receptacle Spacing	6 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Is Pre-Wired	Yes	Wiring Configuration	Single Circuit
Amperage	15 A	Indoor/Outdoor	Indoor
Wiring Method	Hard-Wired	NEMA Configuration Code	5-15R
Mounting Type	On Surface	Voltage	125.0 V
Environmental Conditions	Dry interior locations		