



Wiremold
Wiremold BK20GB509TRUSBA Alternating USB Tamper-Resistant Plugmold Multioutlet System, Black
Part No. BK20GB509TRUSBA



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

- USB charging- Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.
- Multiple colors and finishes- Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.
- Compact design- Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.
- Tamper-resistant receptacles- Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776184433	Country Of Origin	United States
Material	Steel	Product Series	2000 Series
Number of Receptacles	3	Features	USB-A Charging
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Plugmold	Installed Devices	Single Receptacle, USB-A Ports

Dimensions

Product Width US	1.3 in	Product Weight US	2.04 lb
Product Volume US	62.1 cu in	Product Depth US	0.75 in
Product Height US	0.75 in	Product Length US	60.0 in
Receptacle Spacing	9 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Is Pre-Wired	Yes	USB Wattage	15 W
USB Amperage	2.4 A	Wiring Configuration	Single Circuit
Number of USBs	3	Amperage	15 A
Indoor/Outdoor	Indoor	Wiring Method	Hard-Wired
NEMA Configuration Code	5-15R	Mounting Type	On Surface
Voltage	125.0 V	Environmental Conditions	Dry interior locations