



Wiremold
CAF3 Shallow Three Gang Raised Floor Box
Part No. CAF3



The CAF3 Shallow three Gang Raised Floor Box supports up to 3 gangs of communication, power, and/or audio/video devices in two separate compartments. This unique floor box is designed to be compatible in both raised floor and wood floor applications. This compact design is ideal for applications such as retail spaces, education facilities, healthcare facilities, and commercial offices when a shallow floor box is required.

Features & Benefits

Configurable: CAF3 Series floor boxes can be field configured or reconfigured to accommodate power only, communication only, audio/video only or combinations of all three power, communication, audio/video in a single floor box unit.

Hinged door with pull handle: Allows the cover to easily open to a full 180 degrees which provides easy access to devices inside the floor box.

Compact Design: You can now bring your power, communication, and A/V connections in a small package.

Trade Sized Knockouts: (2) 1/2" knockouts, and (2) 3/4" knockouts that can accommodate multiple combinations of power, communication, and audio/video services.

Auto-close egress doors: Cable egress doors lock in position when open, and automatically closes around wires to protect cabling and reduce trip hazards.

Easy to install: For new work and old work applications.

Meets NEC Section 300.22(C): For use in air handling spaces and raised floor plenums

This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786564085782	Country Of Origin	United States
Material	Die-Cast Aluminum	Construction	Assembled
Number of Knockouts	2	Cover Material	Die-Cast Aluminum

Application Sector	Commercial, Education, Healthcare	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box
Dimensions			
Product Width US	6.75 in	Product Weight US	5.4 lb
Product Volume US	161.79 cu in	Product Depth US	7.38 in
Product Height US	3.25 in	Cubic Capacity	20 in³
Knockout Size	1/2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Carpet, Raised, Tile	Service Capacity	Dual
Minimum Floor Depth	3 in	Box Capacity	3 Gangs
Cable Entry	Knockouts & Pass Through	Box Type	Recessed
Number of Outlets	4	Depth Behind Device Plates	1.5 in