



Wiremold
CRFB Series™ CRFB4 Four Gang Round Raised Floor Box
Part No. CRFB4



The CRFB4 Floor Box is a 4 compartment round recessed housing designed to accommodate power, communications, and audio/video services for raised and wood floor applications. Popular applications for the CRFB floor box include: open office environments, conference rooms, computer centers, stages and altars. The CRFB Series floor box can accept the CRFB Series round cover assemblies as well as the 8in Evolution Series Poke-Thru Device covers and are available in six aesthetic colors: black, gray, brass, nickel, bronze, and aluminum. The covers for CRFB housing are sold separately.

Features & Benefits

Accepts the Evolution Series Poke-Thru Covers. The CRFB Series Floor Box has been designed to accept the round 8" Evolution Series Poke-Thru Covers, increasing the ability to match aesthetics throughout the building.

Easy installation in raised and wood floors. CRFB Series Floor Box has been design to be easily installed before or after the floor cover in raised or wood floor applications.

Meets ADA Accessibility Guidelines. Wide trim flange is designed to meet the ADA accessibility Guidelines as it pertains to ADA Standard 4.5, which addresses changes in floor and ground surface levels.

Listed by Underwriters Laboratories Inc. to U.S. and Canadian safety standards for raised floors and wood floors.

Large multi-compartment boxes. Provides adequate wiring capacity for power, communications and audio/video services. The CRFB Series floor boxes have been design to accept a wide range of audio/video devices from most manufacturers.

Flexible, configurable box design. Flexible box design has been improved with removable modules, tunneling feature and increase knockout sizes.

Meets NEC Section 300-22(c). The CRFB Series floor boxes are suitable for use in air handling spaces.

Specifications

General Info

Product Line	Wiremold	Color	Aluminum
Finish	Powder Coat	UPC Number	786564076834
Country Of Origin	China	Material	Die-Cast Aluminum
Construction	Assembled	Cover Style	Surface

Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box
Dimensions			
Product Width US	9.5 in	Product Weight US	13.0 lb
Product Volume US	540.31 cu in	Product Depth US	8.75 in
Product Height US	6.5 in	Cubic Capacity	23.5 in³
Knockout Size	1 in, 1/2 in, 2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Floor Type	Raised, Wood	Service Capacity	Triple
Minimum Floor Depth	6.5 in	Box Capacity	4 Gangs
Cable Entry	Knockout	Number of Outlets	0
Depth Behind Device Plates	2.25 in		