



**Wiremold**  
**Field Wired deQuorum Single Flip Up Unit with USB**  
Part No. DQFF15UST



Field wired unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Comes with a brushed stainless steel finish.

## Features & Benefits

**Sleek, Attractive Design:** Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

**Tamper-Resistant Receptacles:** Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

**New Soft Opening Cover Mechanism:** Opening and closing the cover is quieter and easier with a more professional feel.

**Expanded Configuration Options:** Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

**UL Spill Water Protection:** Meets or exceeds UL 111 - Outline of Investigation for Multioutlet Assemblies. Eliminates risk of shock or short circuiting due to moisture entering device.

**USB Charging Capability:** Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

**Multiple Cover Finish Options:** Durable black powder coat and brushed stainless steel finishes blend with most decors.

**cULus Listed:** Meets UL US and Canadian Safety standards for Multioutlet Assemblies (File E15191, Guide PVGT).

## Specifications

### General Info

|              |              |                       |                 |
|--------------|--------------|-----------------------|-----------------|
| Product Line | Wiremold     | Color                 | Stainless Steel |
| UPC Number   | 786776186819 | Country Of Origin     | Mexico          |
| Material     | Aluminum     | Number of Receptacles | 1               |
| Construction | Various      | Features              | USB-A Charging  |

|                                       |                                                                                                                             |                         |                                                                                       |
|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|-------------------------|---------------------------------------------------------------------------------------|
| Outlet Type                           | Tamper-Resistant                                                                                                            | Application Sector      | Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit |
| Standard                              | cULus Multioutlet Assembly File E15191 Guide PVGT Listed to US and Canadian Safety Standards. Meets Article 390 of the NEC. | Warranty Type           | 1-Year from Installation or 2-Years from Day of Sale                                  |
| Type                                  | Flip Up                                                                                                                     |                         |                                                                                       |
| Dimensions                            |                                                                                                                             |                         |                                                                                       |
| Product Width US                      | 4.75 in                                                                                                                     | Product Weight US       | 2.3 lb                                                                                |
| Product Length US                     | 5.625 in                                                                                                                    | Internal Depth          | 3.25 in                                                                               |
| Listing Agencies / 3rd Party Agencies |                                                                                                                             |                         |                                                                                       |
| cULus ListingNumber                   | E15191                                                                                                                      | cULus Listed            | Yes                                                                                   |
| Trade Programs                        |                                                                                                                             |                         |                                                                                       |
| USMCA                                 | Yes                                                                                                                         |                         |                                                                                       |
| Additional Information                |                                                                                                                             |                         |                                                                                       |
| RoHS Compliant                        | Yes                                                                                                                         |                         |                                                                                       |
| Technical Information                 |                                                                                                                             |                         |                                                                                       |
| USB Wattage                           | 15 W                                                                                                                        | USB Amperage            | 3.1 A                                                                                 |
| Cord Length                           | 6 ft                                                                                                                        | Number of USBs          | 1                                                                                     |
| Amperage                              | 15 A                                                                                                                        | Cable Entry             | Bottom                                                                                |
| Wiring Method                         | Hard-Wired                                                                                                                  | NEMA Configuration Code | 5-15R                                                                                 |
| Mounting Type                         | Recessed                                                                                                                    | Cutout Shape            | Rectangular                                                                           |

---

Voltage

125.0 V

---