



Wiremold
Field Wired deQuorum Single Flip Up Unit with USB
Part No. DQFF20UBK



Field wired unit includes one (1) 20A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Comes with a black powder coat finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets or exceeds UL 111 - Outline of Investigation for Multioutlet Assemblies. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian Safety standards for Multioutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776186826	Country Of Origin	Mexico
Material	Aluminum	Number of Receptacles	1
Features	USB-A Charging	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

Type	Flip Up		
Dimensions			
Product Weight US	2.3 lb	Internal Depth	3.25 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
USB Wattage	15 W	USB Amperage	3.1 A
Cord Length	6 ft	Number of USBs	1
Amperage	20 A	Wiring Method	Hard-Wired
NEMA Configuration Code	5-20R	Mounting Type	Recessed
Cutout Shape	Rectangular	Voltage	125.0 V