



Wiremold
Cord Ended deQuorum™ Single-Flip Up Unit
Part No. DQFP15BK



Unit includes one (1) 15A black tamper-resistant duplex receptacle. Unit comes with a 6' (1.83m) cord. Comes with a black powder coat finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XBYS) and Multitoutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776184549	Country Of Origin	Mexico
Material	Aluminum	Number of Receptacles	1
Construction	Die Cast	Outlet Type	Tamper-Resistant

Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit	Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Flip Up
Dimensions			
Product Width US	4.75 in	Product Weight US	3.9 lb
Product Length US	5.625 in	Internal Depth	3.25 in
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Cord Length	6 ft	Amperage	15 A
Cable Entry	Below	Wiring Method	Cord-ended
NEMA Configuration Code	5-15R	Mounting Type	Recessed
Cutout Shape	Rectangular	Voltage	125.0 V