



Wiremold
Cord Ended deQuorum™ Single Flip Up Unit with USB
Part No. DQFP15UBK



Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Unit comes with a 6' (1.83m) cord. Comes with a black powder coat finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XBY5) and Multitoutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776184587	Country Of Origin	Mexico
Material	Aluminum	Number of Receptacles	1
Construction	Die Cast	Features	USB-A Charging

Outlet Type	Tamper-Resistant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit
Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Flip Up		
Dimensions			
Product Width US	4.75 in	Product Weight US	3.9 lb
Product Length US	5.625 in	Internal Depth	3.25 in
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
USB Wattage	15 W	USB Amperage	3.1 A
Cord Length	6 ft	Number of USBs	1
Amperage	15 A	Cable Entry	Below
Wiring Method	Cord-ended	NEMA Configuration Code	5-15R
Mounting Type	Recessed	Cutout Shape	Rectangular

Voltage	125.0 V
---------	---------
