



Wiremold
Discontinued - DS4000 External Elbow Fitting
Part No. DS4018-DG



90 degree full capacity divided external elbow that provides a 2" (51mm) cable bend radius for fiber optic/UTP/STP installations. One pair of DS4001 Couplings included.

Features & Benefits

90 degree full capacity divided external elbow that provides a 2" (51mm) cable bend radius for fiber optic/UTP/STP installations. One pair of DS4001 Couplings included.

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786776081787	Country Of Origin	United States
Application Sector	Commercial	Standard	cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Blank Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Raceway

Dimensions

Product Weight US 0.29 lb

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E41751	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Voltage	600.0 V
---------	---------
