



Wiremold
Rack Mount 120V/15A/6 front 90 degree O/L /lighted switch/6' cord
Part No. J60B0B-90



Six front outlets, 15A, receptacles rotated 90 degrees and spaced to accommodate transformers. 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm).

Features & Benefits

Six front 20A outlets, 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm).

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776104189	Country Of Origin	Mexico
Material	Steel	Product Series	Rack Mount
Receptacle Type	Simplex	Number of Receptacles	6
Features	Lighted Switch	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	1.75 in	Product Weight US	3.0 lb
Product Depth US	2.57 in	Product Length US	19.0 in
Receptacle Spacing	1.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Cord Length	6 ft
Amperage	15 A	Enclosure Type	Steel
Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Rack Mounting
Location Rating	Dry	Voltage	125.0 V
Environmental Conditions	Dry interior locations		