



Wiremold
Plug-In Outlet Center Unit / Polymeric/120V/15A/6 O/L /lighted switch/15' cord
Part No. P6-15



P6 includes six outlets in a putty white impact-resistant housing. Delivers 15A of power with a lighted switch. Includes 15ft 14/3 SJT white cord with NEMA 5-15 plug.

Features & Benefits

This product meets the material restrictions of RoHS

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776043488	Country Of Origin	China
Product Series	Plug-In Outlet Center	Receptacle Type	5-15R
Number of Receptacles	6	Features	Lighted Switch
Application Sector	Commercial, Residential	Standard	UL Listed: File E66421, Guide XBYS
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	1.12 in	Product Weight US	2.2 lb
Product Height US	2.19 in	Product Length US	12.37 in
Receptacle Spacing	1.25 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	LR90520
------------	-----	-----------------	---------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Cord Length	15 ft	Amperage	15 A
-------------	-------	----------	------

Wiring Method	Cord-ended	NEMA Configuration Code	5-15P, 5-15R
---------------	------------	-------------------------	--------------

Mounting Type	Screw Mount	Voltage	125.0 V
---------------	-------------	---------	---------