



Wiremold
Plug-In Outlet Center Unit / 120V/15A/6 O/L /lighted switch/6' cord/Value Grade Surge
Part No. PR610N



Basic surge protection. Six outlets, lighted switch, impact-resistant putty white polymetric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Maximum surge current 6500 Amps. 11 3/4" x 2 1/4" x 1 1/2 (298mm x 57mm x 38mm). Keyhole mounting.

Features & Benefits

Basic surge protection. Six outlets, lighted switch, impact-resistant putty white polymetric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug.

Maximum surge current 6500 Amps. 11 3/4" x 2 1/4" x 1 1/2 (298mm x 57mm x 38mm). Keyhole mounting.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776130072	Country Of Origin	China
Product Series	Perma Power	Number of Receptacles	6
Features	Lighted Switch, Surge Protection	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	11.73 in	Product Weight US	1.5 lb
Product Height US	1.5 in	Product Length US	2.24 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E111219	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Cord Length	6 ft	Connection	Cord-ended
Class	75	Amperage	15 A
Short Circuit Rating	6500A	Wiring Method	Cord-ended
NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Snap-on, Slide-off
Type of Indicators	Light	Voltage	120.0 V