



Wiremold
Plug-In Outlet Center Unit / Rack Mount 120V/20A/6 rear O/L /lighted switch/6' cord/Computer Grade Surge
Part No. R5BZ20



Six 20A rear outlets, on/off switch. 6' (1.8m) cord. Perma Power computer grade surge protection.

Features & Benefits

Six 20A rear outlets, on/off switch. 15' (4.6m) cord. Perma Power computer grade surge protection.

Specifications

General Info			
Product Line	Wiremold	Color	Black
UPC Number	786776121063	Country Of Origin	Mexico
Material	Aluminum	Product Series	Perma Power
Number of Receptacles	6	Features	Surge Protection
Application Sector	Commercial, Residential	Standard	cULus Recognized: File E66421: Guide XBYS2, XUHT2, VZCA4
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC
Dimensions			
Product Width US	19.0 in	Product Weight US	3.1 lb
Product Height US	2.57 in	Product Length US	1.75 in
Receptacle Spacing	1.5 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Phase	Single Stage	Cord Length	6 ft
Connection	Cord-ended	Class	75
Amperage	20 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Wiring Method	Cord-ended
NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Rack Mounting
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V		