



Wiremold
Plug-In Outlet Center Unit / Rack Mount 120V/15A/8 rear O/L /lighted switch/15' cord/Computer Grade Surge
Part No. R8BZ-15



Eight rear outlets, lighted switch, 15A. Receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 15' (4.6m) cord. Perma Power computer grade surge protection.

Features & Benefits

Eight rear outlets, lighted switch, 15A. Receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 15' (4.6m) cord. Perma Power computer grade surge protection.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776012217	Country Of Origin	China
Material	Aluminum	Product Series	Perma Power
Number of Receptacles	8	Features	Lighted Switch, Surge Protection
Application Sector	Commercial, Residential	Standard	cULus Recognized: File E66421: Guide XBYS2, XUHT2, VZCA13
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Width US	19.0 in	Product Weight US	3.1 lb
Product Height US	2.57 in	Product Length US	1.75 in
Receptacle Spacing	1.31 in, 2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single Stage	Cord Length	10 ft
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	36000 Amps (12000 Amps L-N 12000 Amps L-G 12000 Amps N-G)
Response Time	<1 ns	Wiring Method	Cord-ended

NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Rack Mounting
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V		