



radiant Collection
radiant® FPC USB A/C, 10FT, NI 2 TR OL, 2 USB CHARGING PORTS
Part No. RDZCNI10



radiant Furniture Power Centers bring a sleek, modern design with the functionality of USB and traditional power together. Quick and easy installation means nearly every piece of furniture can be powered up and ready to recharge devices. A sleek design and tamper-resistant receptacles bring your furniture a step above ordinary.

Features & Benefits

Simply cut an opening, insert, tighten clamps, snap on the bezel and plug in.

Specifications

General Info

Product Line	Wiremold	Color	Nickel
UPC Number	786776192483	Country Of Origin	China
Material	Plastic	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant
Application Sector	Commercial Office, Education, Hospitality, Multi-Dwelling Unit, Municipal, Retail, Transportation, Worship	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Furniture Power Center		

Dimensions

Product Width US	5.625 in	Product Weight US	1.88 lb
Product Depth US	2.125 in	Product Height US	2.5 in

Internal Depth	2 in
----------------	------

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes
------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

USB Wattage	15 W	USB Amperage	3.1 A
Wiring Configuration	Single Circuit	Cord Length	10 ft
Number of USBs	2	Amperage	15 A
Wiring Method	Cord-ended	NEMA Configuration Code	5-15R
Mounting Type	Recessed	Cutout Shape	Rectangular
Voltage	125.0 V		