



radiant Collection
Discontinued - Furniture Power Basic Power Unit with 10' Cord - Nickel
Part No. RDZNI10



radiant Furniture Power Centers bring a sleek, modern design with the functionality of USB and traditional power together. Quick and easy installation means nearly every piece of furniture can be powered up and ready to recharge devices. A sleek design and tamper-resistant receptacles bring your furniture a step above ordinary.

Features & Benefits

Simply cut an opening, insert, tighten clamps, snap on the bezel and plug in. A compact, low profile design mounts quickly into many surfaces using screw clamps instead of wood screws.

Safe for spills and ready to mount in horizontal surfaces like table tops

Two USB charging ports (5V, 3.1A total) to charge mobile devices as quickly as possible.

Two tamper-resistant receptacles to protect yourself and your devices from damage or risk of injury.

Version with 10' cord available in black, white, and nickel.

Version 2 models feature an optional push button switch that controls a cord-connected lighting fixture.

The pass-thru plug allows you to plug another device such as a lamp into the back of the furniture power unit plug, ensuring you don't lose an outlet.

Complies with part 15 of the FCC Rules and is ETL Listed to both US and Canadian safety standards.

Specifications

General Info

Product Line	Wiremold	Color	Nickel
UPC Number	786776192094	Country Of Origin	China
Material	Plastic	Number of Receptacles	2
Features	USB-A Charging	Outlet Type	Tamper-Resistant
Application Sector	Commercial Office, Education, Hospitality, Multi-Dwelling Unit, Municipal, Retail, Transportation, Worship	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

Type	Furniture Power Center		
Dimensions			
Product Width US	5.625 in	Product Weight US	1.74 lb
Product Depth US	2.125 in	Product Height US	2.5 in
Internal Depth	2 in		
Listing Agencies / 3rd Party Agencies			
ETL Listed	Yes	ETL ListingNumber	103010048BOX-001
Additional Information			
RoHS Compliant	Yes		
Technical Information			
USB Wattage	15 W	USB Amperage	3.1 A
Wiring Configuration	Single Circuit	Cord Length	10 ft
Number of USBs	2	Amperage	15 A
Wiring Method	Cord-ended	NEMA Configuration Code	5-15R
Mounting Type	Recessed	Cutout Shape	Rectangular
Voltage	125.0 V		