



Wiremold
Plug-In Outlet Center Unit / 120V/15A/5 O/L /6' cord
Part No. UL100BC



Five outlets, rugged gray aluminum housing, 15A. 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 9 1/4" (235mm). Receptacle center-to-center 1 1/4" (32mm). Snap-on, slide-off mounting.

Features & Benefits

Five outlets, rugged gray aluminum housing, 15A. 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 9 1/4" (235mm). Receptacle center-to-center 1 1/4" (32mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	Color	Aluminum, Gray
UPC Number	786776043068	Country Of Origin	Mexico
Material	Aluminum	Product Series	Plug-In Outlet Center
Receptacle Type	Simplex	Number of Receptacles	5
Features	Resettable Circuit Breaker	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	2.0 in	Product Weight US	1.5 lb
Product Depth US	1.89 in	Product Length US	9.25 in

Receptacle Spacing	1.25 in
--------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Single	Cord Length	6 ft
Amperage	15 A	Enclosure Type	Aluminum
Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Slide-off, Snap-on
Location Rating	Dry	Voltage	125.0 V
Environmental Conditions	Dry interior locations		