



Wiremold
Plug-In Outlet Center Unit / 120V/15A/72 long/24 O/L /lighted switch/15' cord
Part No. UL2065BD



Twenty-four outlets, rugged gray aluminum housing, 15A, lighted switch, 15' (4.6m) 14/3 SJT black cord with NEMA5-15 plug. Length 72" (1.8m). Receptacle center-to-center 2 1/2" (64mm). Snap-on, slide-off mounting.

Features & Benefits

Twenty-four outlets, rugged gray aluminum housing, 15A, lighted switch, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 72" (1.8m). Receptacle center-to-center 2 1/2" (64mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	Color	Aluminum, Gray
UPC Number	786776047745	Country Of Origin	Mexico
Material	Aluminum	Product Series	Plug-In Outlet Center
Receptacle Type	Simplex	Number of Receptacles	24
Features	Resettable Circuit Breaker	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	2.0 in	Product Weight US	6.2 lb
Product Length US	72.0 in	Receptacle Spacing	2.5 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Technical Information

Phase	Single	Cord Length	15 ft
-------	--------	-------------	-------

Amperage	15 A	Enclosure Type	Aluminum
----------	------	----------------	----------

Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
----------------	--------	---------------	------------

NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Snap-on, Slide-off
-------------------------	--------------	---------------	--------------------

Location Rating	Dry	Voltage	125.0 V
-----------------	-----	---------	---------

Environmental Conditions	Dry interior locations
--------------------------	------------------------