



Wiremold
20GB512 Steel Plugmold® Multioutlet System
Part No. WH20GB512



5' Plugmold Multioutlet System with 5 single outlets, GB

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776074529	Country Of Origin	United States
Material	Steel	Product Series	2000 Series

Number of Receptacles	5	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard	cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.		Warranty Type 1-Year from Installation or 2-Years from Day of Sale
Type	Plugmold	Installed Devices	Single Receptacle
Dimensions			
Product Width US	1.3 in	Product Weight US	3.03 lb
Product Depth US	0.75 in	Product Height US	0.75 in
Product Length US	60.0 in	Receptacle Spacing	12 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Is Pre-Wired	Yes	Wiring Configuration	Single Circuit
Amperage	15 A	Indoor/Outdoor	Indoor

Wiring Method	Hard-Wired	NEMA Configuration Code	5-15R
Mounting Type	On Surface	Voltage	125.0 V
Environmental Conditions	Dry interior locations		