



Wiremold
Desktop Power Center Slim, 3 Outlets, USB A/C, Black, 6ft Cord
Part No. WSPC320CBK



Desktop Power Center with two (2) or three (3) 15A tamper resistant power receptacles and two (2) smart USB ports, one (1) USB-A and one (1) USB-C, that provide 3.1A. Includes a screw-in mounting plate for forward-facing outlets, under-table mount bracket, and clamp mounting kit. Available with either a 6' (1.83m) or 10' (3.05m) power cord.

Features & Benefits

Multiple options: Two versions with reliable power and charging – one with three (3) tamper-resistant power outlets and two (2) USB charging ports (3.1A) and one with two (2) tamper-resistant power outlets and two (2) USB charging ports (3.1A).	Intelligent and energy efficient: Smart charging capability that recognizes devices and when to shut off during peak loads.
Easy connection to power sources: 6' (1.83m) or 10' (3.05m) 14 gauge cord easily reaches walls and floors.	Simple and flexible installation: Mounting kits include options for both horizontal and vertical applications.
Less clutter, more functionality: A sleek slim design fits unobtrusively on work surfaces.	Seamlessly blends into your space: Two color choices that work with any environment.
Table Thickness: Supports tables from 0.5" to 1.5" for the clamp mount. Under table bracket mount supports 1" to 1.5".	Included Mounting Kit: Includes several mounting options for use under and above table surfaces for any environment.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776192575	Country Of Origin	China
Material	Plastic	Number of Receptacles	3
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

Type	Desktop Power Center		
Dimensions			
Product Width US	2.25 in	Product Weight US	1.952 lb
Product Height US	2.25 in	Product Length US	6.0 in
Listing Agencies / 3rd Party Agencies			
ETL Listed	Yes	ETL ListingNumber	103010043BOX-001
Additional Information			
RoHS Compliant	Yes		
Technical Information			
USB Wattage	15 W	USB Amperage	3.1 A
Wiring Configuration	Single Circuit	Cord Length	6 ft
Number of USBs	2	Amperage	15 A
Wiring Method	Cord-ended	NEMA Configuration Code	5-15R
Mounting Type	On Surface	Voltage	125.0 V