



Wiremold
Charging Station with 4000K Area Light, 2-Gang, (1) Duplex GFCI, (1) 4-Port USB-A Outlet - Silver
Part No. XCSLF2GRU-SV



Charging Station with Area Light is a charging station with an LED light to eliminate the need for a stand-alone bollard. Perfect for use as pathway lighting in educational, corporate and recreational applications.

Features & Benefits

Warm light for the perfect ambiance for your space

2- or 3-Gang Options: Customize the station with two or three gangs of devices to meet your facility's unique needs. Available in prewired or unwired versions.

Outdoor-Rated Construction: Rugged aluminum form design for durability in outdoor locations.

Durable, Premium Finishes: Available in three outdoor-rated finishes to complement your space

A/V & Communication Compatible: Enables station to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

Device Shelves: Add up to two pairs of shelves to hold mobile devices while charging

Door Options: Interior illuminates when door is opened. Or, select lockable door for added security or to ensure use is limited to facility personnel.

ADA Compliant: Meets all specifications for ADA guidelines

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786776186048	Country Of Origin	Mexico
Material	Aluminum	Number of Receptacles	1
Features	USB-A Charging	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit
Standard	cULus Listed, File Number E479489, Guide PUPR	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

Type	Charging Stations	Installed Devices	4-Port USB-A, GFCI
Dimensions			
Product Width US	6.0 in	Product Weight US	43.0 lb
Product Height US	48.0 in	Product Length US	8.0 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E479489	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Operating Temperature Min	-22 °F	Is Pre-Wired	Yes
Service Capacity	Single	Number of USBs	1
Operating Temperature Max	140 °F	Number of Gangs	2
Amperage	20 A	Enclosure Type	NEMA 3R
Lumens	457 lm	NEMA Configuration Code	5-20R
Number of Channels	1	Lighting Types	Area Light
Operating Temperature	-22°F-140°F		