



Wiremold
Charging Station, 3-Gang, (1) Duplex GFCI and (2) 4-Port USB-A Outlets - Black
Part No. XCSPP3GRUU-BK



The Power Pedestal is ideal for areas that are already illuminated, such as outdoor dining areas. Shorter height enables use besides tables or as a lower-profile solution in landscaping. Station includes one duplex GFCI receptacles and two 4-Port USB Outlets.

Features & Benefits

2- or 3-Gang Options – Customize the station with two or three gangs of devices to meet your facility's unique needs. Prewired versions include weather-resistant GFCI outlets and 4-port USB outlets. Also available unwired.

Durable, Premium Finishes – Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

Add up to two pairs of shelves to hold mobile devices while charging

Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

Outdoor-Rated Construction – Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.

Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices.

Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776186352	Country Of Origin	Mexico
Material	Aluminum	Number of Receptacles	1
Features	USB-A Charging	Outlet Type	Weather-Resistant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit	Standard	cULus Listed, File Number E479489, Guide PUPR

Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Charging Stations
Installed Devices	4-Port USB-A, GFCI		
Dimensions			
Product Width US	6.0 in	Product Height US	34.0 in
Product Length US	8.0 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E479489	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	-31 °F	Is Pre-Wired	Yes
Service Capacity	Single	Number of USBs	2
Operating Temperature Max	140 °F	Number of Gangs	3
Amperage	20 A	Enclosure Type	NEMA 3R
NEMA Configuration Code	5-20R	Number of Channels	1
Lighting Types	No Light	Operating Temperature	-31°F-140°F