



Wiremold
Outdoor Rooftop Box, (2) 20A Weather-Resistant GFCI Duplex Receptacles, Black Cover
Part No. XFB2GRRBK



The Outdoor Rooftop Box is an innovative solution that provides convenient access to power on raised rooftop deck environments. Install power access anywhere along a deck's surface. This rooftop box is perfect for outdoor events or furniture requiring access to power, eliminating the need for extension cords along the decking surface and providing greater flexibility in power distribution on rooftops. The box is designed to be installed flush alongside rooftop pavers and features a hinged top self-closing cover. The internal rotating outlet box can be rotated upwards when power access is needed and rotates downward when in-use. The rooftop box supports (2) 20A weather-resistant, GFCI duplex receptacles. The prewired unit comes with receptacles pre-installed and wire leads for wiring up to nearby junction boxes.

Features & Benefits

Easy Installation: The outdoor rooftop box is designed to integrate seamlessly into raised floor patio systems commonly used on rooftops.

Flush, Durable Design: The outdoor rooftop box sits flush with the floor and incorporates a slip resistant surface to prevent safety issues.

Shallow Design: Can be used in any raised floor system with 7" or more of space from top of floor to roof surface.

While-in-Use Design: Plug in your devices, route cables through egress and close the cover for NEMA 3R protection while in use.

1000Lb Load Rating: Capable of withstanding loads of 1000lbs, this box can handle loads from foot traffic, drink carts or dollies suppling the outdoor area.

Self-Closing Cover: Self-closing to prevent users from leaving the receptacles exposed to the elements and open cover tripping hazards.

Match Space Aesthetic: Available in both gray and black cover finishes to complement rooftop decking.

2-Gangs of Capacity: Unwired unit provides 2-gangs of capacity. Prewired unit includes two 20A duplex weather-resistant GFCI outlets.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776198676	Country Of Origin	China
Material	Plastic	Conduit Size	1/2 in
Number of Receptacles	2	Installation Location	Rooftop Pavers
Application Sector	Commercial, Hospitality, Multi-Dwelling Unit	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Installed Devices	WR GFCI		

Dimensions

Product Width US	8.0 in	Product Weight US	6.75 lb
------------------	--------	-------------------	---------

Product Height US	6.25 in	Product Length US	11.75 in
-------------------	---------	-------------------	----------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	-22 °F	Is Pre-Wired	Yes
Service Capacity	Single	Floor Thickness Supported	0.75 to 2.25 in
Operating Temperature Max	122 °F	Number of Gangs	2
Amperage	20 A	Enclosure Type	NEMA 3R
Load Capacity	1000 lb	NEMA Configuration Code	5-20R
Number of Channels	1	Operating Temperature	-22°F-122°F
Relative Humidity	Up to 95% Non-condensing		