




adorne Collection
adorne® 277V Paddle Switch, Half-Size, Magnesium, with Microban®
Part No. ASPD1531M277



A modern twist on classic up-and-down light switch control, the Paddle Switch lets you turn lights on and off with ease and style. Use this 277V switch on its own to control a light or fixture from a single location, or pair with a second switch for 3-way control of a single light source from two locations. Combine this half-size switch with other half or standard-sized devices to fit more functionality in a single decorative wall plate.

This switch* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Combine with another half or standard-sized device to fit into a 1-Gang or 1-Gang+ Wall Plate.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007052923
Country Of Origin	China	Material	Polycarbonate
Features	Antimicrobial Protection	Switch Type	Paddle

Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Warranty Type	Limited Lifetime Warranty
Type	Switch		
Dimensions			
Product Width US	1.5 in	Product Depth US	0.89 in
Product Height US	1.77 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140597	cULus Listed	Yes
Technical Information			
Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	20 A	Number of Poles	3-Way, Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Box	Location Rating	Dry
Wire Connection Type	Internal Pressure Plates	Voltage	277.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		