




adorne Collection
adorne® 277V 4-Way Paddle Switch, White, with Microban®
Part No. ASPD1542W277



A modern twist on classic up-and-down switch control, the 277V 4-way Paddle Switch lets you turn lights on and off with ease. Pair this light switch with another to use as a remote switch for control a single light source from multiple locations.

This switch* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Combine with other switches or dimmers in 4-way applications, allowing control of a single light source from multiple locations.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007052954
Country Of Origin	Mexico	Material	Polycarbonate
Features	Antimicrobial Protection	Switch Type	Paddle
Number of Switches	1	Application Sector	Hospitality, Residential

Wall Plate Included	No	Warranty Type	Limited Lifetime Warranty
Type	Switch		
Dimensions			
Product Width US	1.77 in	Product Depth US	1.5 in
Product Height US	1.77 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140597	cULus Listed	Yes
Technical Information			
Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	15 A	Number of Poles	4-Way
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Box	Location Rating	Dry
Wire Connection Type	Internal Pressure Plates	Voltage	277.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		