




adorne Collection
Discontinued - adorne® Touch™ Wi-Fi Ready Master Switch, Magnesium
Part No. ASTH155RMM1



Intuitive touch technology combines with Wi-Fi-Readiness in this sleek lighting control option. The Touch Wi-Fi Ready Master Switch is a programmable light switch that pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Turn lights on/off with the touch of a finger, or create custom lighting scenes through the Legrand Lighting Control app for smartphones and tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with the Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Pair with a Touch Wi-Fi Ready Remote Switch for 3-way control.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	804428065814	Country Of Origin	China
Material	Lexan, Polycarbonate	Features	Smart Lighting
Switch Type	Touch	Number of Switches	1
Works With	Amazon Alexa, Google Assistant, Radio Frequency	Application Sector	Residential
Standard	UL 508, FCC cULus, RoHS	Warranty Type	1-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon
Number of Poles	3-Way, Multi-Location, Single Pole	Requires Neutral Wire	Yes
Wattage	1800 W	Mounting Type	Box
Supply Voltage	120 V	Location Rating	Dry
Connection Type	Internal Pressure Plates	Environmental Conditions	0 to 80% (relative humidity, non-condensing)