



Great for places where you might often forget to the lights off, like bathrooms or basements. This timer light switch features Manual On/Timed Off control, so you can easily turn lights on when entering a room and then let yourself go worry-free. Just preset the timer switch to turn lights off automatically at a specific time, like after you leave for work or to take the kids to school.

This switch* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Uses SensaSwitch technology to automatically turn lights off after you leave on a timed delay. (Time delay options include 10, 20, 30 or 60 minutes.)

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007023008
Country Of Origin	China	Material	Lexan, Polycarbonate
Features	Antimicrobial Protection, Timer	Switch Type	Motion Sensor

Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	cULus
Warranty Type	Limited Lifetime Warranty	Type	Switch
Dimensions			
Product Width US	1.77 in	Product Depth US	1.85 in
Product Height US	2.66 in		
Technical Information			
Load Rating	120V 600W	Connection Location	Back Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Number of Poles	3-Way, Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Timing Range	10-60 minutes	Mounting Type	Box
Location Rating	Dry	Wire Connection Type	Internal Pressure Plates
Voltage	120.0 V	Load Type	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon