




adorne Collection
adorne® Smart Switch with Netatmo, Magnesium
Part No. WNAL10M1



Control lights at the wall with this sleek sofTap Registered switch, or through the intuitive app. Pair this smart switch with the Wireless Smart Switch with Netatmo to gain easy 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne Registered with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart light switches, smart dimmer light switches and smart outlets to build a solution that perfectly fits a home's unique space and needs. Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED.

Controls lights, from anywhere, via smartphones and tablets through the Legrand Home + Control app. Schedule lights to turn on/off automatically, create groups, set scenes, monitor energy usage and more.

Installs easily in place of an existing single-pole switch or dimmer (neutral wire required). For easy 3-way control, pair with a Wireless Smart Switch with Netatmo.

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including wireless switches and dimmers).

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007380798
Country Of Origin	China	Material	Polycarbonate
Features	Smart Lighting, With Netatmo	Switch Type	sofTap
Number of Switches	1	Works With	Amazon Alexa, Apple Home Kit, Google Home

Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	2-Year Limited Warranty	Type	Switch
Dimensions			
Product Width US	1.73 in	Product Depth US	1.53 in
Product Height US	4.19 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E350248	cULus Listed	Yes
FCC Compliant	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Connection	Wireless	Number of Gangs	1
Amperage	15 A	Number of Poles	Multi-Location, Single Pole
Wire Size	#14 - #10 AWG	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	In-Wall
Location Rating	Dry	Wire Connection Type	Internal Terminal Screw
Voltage	120 VAC		