




adorne Collection
adorne® Wireless Smart Switch with Netatmo, Magnesium
Part No. WNAL23M1



Pair this sofTap Registered battery-operated smart light switch with an adorne Smart Switch with Netatmo then add to any wall to control the same light from an additional location – no wires or tools needed. Use the included adhesive to mount anywhere in minutes. Perfect for rooms not wired for 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne Registered with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer switches and smart outlets to build a solution that perfectly fits any space and need. Made exclusively for use with Wall Plates from the adorne Registered Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED. Must also be paired with an adorne or radiant Smart Switch with Netatmo or a Smart Plug-In Switch with Netatmo.

Perfect solution for adding 3-way control when paired with a Smart Switch with Netatmo.

Installs easily, without wires or cutting, for ultimate flexibility. Simply mount to any wall for long-lasting, battery-powered control.

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including wireless switches and dimmers).

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Metallic	UPC Number	785007380958
Country Of Origin	China	Material	Polycarbonate
Features	Battery-Operated, Smart Lighting, With Netatmo	Switch Type	sofTap

Number of Switches	1	Works With	Amazon Alexa, Apple Home Kit, Google Home
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	2-Year Limited Warranty	Type	Switch
Dimensions			
Product Width US	1.79 in	Product Depth US	0.24 in
Product Height US	4.68 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E95219	cULus Listed	Yes
FCC Compliant	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Connection	Wireless	Number of Gangs	1
Number of Poles	Multi-Location	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Surface Mount, Wall Box
Location Rating	Dry	Wire Connection Type	Battery Powered
Voltage	3.0 V		