



radiant Collection
radiant® Smart 15A Outlet with Netatmo, Nickel
Part No. WNRR15NI



With this 15A smart outlet, take control lamps or small appliances from anywhere. (One outlet is app-controlled, the other is always on.) Monitor and manage energy usage through the app to reduce utility cost and waste. Part of the radiant Registered with Netatmo solution. Smart Lighting lets you control lights and power, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant Registered with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, dimmers and outlets to build a solution that perfectly fits a home's unique space and needs. Options even include wireless smart switches and dimmers for easily adding 3-way control. Screwless Wall Plates from the radiant Registered Collection included.

Features & Benefits

Smart Gateway REQUIRED.

Enables control of lamps or appliances via smartphones and tablets using the Legrand Home + Control app. Schedule them to turn on/off automatically, create groups, set scenes and monitor energy usage.

Installs easily in place of an existing 15A outlet. Can be wired to extend control to all outlets downstream or load-side. One outlet is app-controlled, the other is always on.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with black "invisi-shutters" for an invisible effect.

Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
Finish	Metallic	UPC Number	785007289602
Country Of Origin	China	Number of Receptacles	2

Features	With Netatmo	Works With	Amazon Alexa, Apple Home Kit, Google Home
Outlet Type	Wi-Fi Ready	Application Sector	Commercial, Multi- Dwelling Unit, Residential
Standard	RoHS, FCC, IC, cULus, UL	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	2.25 in	Product Weight US	0.18 lb
Product Volume US	54.0 cu in	Product Depth US	4.0 in
Product Height US	6.0 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E495025	cULus Listed	Yes
FCC Compliant	Yes		
Additional Information			
RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Technical Information			
Seismic Tested	No	Is Tamper-Resistant	Yes
Connection	Wired	Number of Wires	2
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Wire Size	#14 - #10 AWG
Is Weather Resistant	No	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box

Wire Connection Type	Screw Terminals
----------------------	-----------------
