




Wiremold  
886B Stamped Steel Floor Box  
Part No. 886B



The 880 Series Floor Box provides an excellent solution for the low density power or communication requirements in open space areas. The 880 Series brings the power or communication service directly to the workstation. The 880 Series comes in a cast iron version for on grade applications and an economical stamped steel version for above grade applications. The 880 Series is supported by one of the most complete lines of brass, brushed aluminum, and nonmetallic activations in the industry. Some applications for the 880 Series Floor Box are retail facilities, commercial offices, hotels, and financial institutions.

## Features & Benefits

The 880 Series Floor Box provides an excellent solution for the low density power or communication requirements in open space areas.

Brings the power or communication service directly to the workstation.

Comes in a cast iron version for on grade applications and an economical stamped steel version for above grade applications.

Supported by one of the most complete lines of brass, brushed aluminum, and nonmetallic activations in the industry.

Some applications for the 880 Series Floor Box are retail facilities, commercial offices, hotels, and financial institutions.

## Specifications

### General Info

|                   |                                                                                           |                    |                                                         |
|-------------------|-------------------------------------------------------------------------------------------|--------------------|---------------------------------------------------------|
| Product Line      | Wiremold                                                                                  | UPC Number         | 786564540403                                            |
| Country Of Origin | Mexico                                                                                    | Material           | Steel                                                   |
| Construction      | Assembled                                                                                 | Application Sector | Commercial,<br>Education,<br>Healthcare,<br>Hospitality |
| Standard          | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. | Warranty Type      | 1-Year from Installation or 2-Years from Day of Sale    |
| Type              | Floor Box                                                                                 |                    |                                                         |

### Dimensions

|                  |        |                   |              |
|------------------|--------|-------------------|--------------|
| Product Width US | 4.8 in | Product Weight US | 2.038 lb     |
| Product Depth US | 4.8 in | Product Height US | 2.75 in      |
| Cubic Capacity   | 39 in³ | Knockout Size     | 1 in, 1/2 in |

Listing Agencies / 3rd Party Agencies

|                     |       |              |     |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

|              |                        |                            |          |
|--------------|------------------------|----------------------------|----------|
| Floor Type   | Carpet, Concrete, Tile | Service Capacity           | Single   |
| Box Capacity | 1 Gang                 | Cable Entry                | Knockout |
| Box Type     | Above-Grade            | Depth Behind Device Plates | 2.25 in  |